



More information on the website
mirror.radwag.com/en/info,w1,NZ3

XA 120/250.5Y Analytical Balance

WL-110-1002



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- Autotest
- Dosing
- Percent Weighing
- Parts counting
- Peak hold
- Formulation
- Newton unit measurement
- Statistics
- Checkweighing
- IR sensors
- Under-pan weighing
- GLP Procedures
- Animal weighing
- Pipettes Calibration
- Air density correction
- Density determination
- Moveable range
- Differential weighing
- Ambient conditions monitoring
- Statistical Quality Control
- Packaged Goods Control
- ALIBI Memory
- Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	120 / 250 g
Minimum load	1 mg

Metrological parameters	
Readability [d]	0.01 / 0.1 mg
Verification unit [e]	1 mg
Tare range	-250 g
Minimum weight (USP)	10 mg
Minimum weight (U=1%, k=2)	1 mg
Standard repeatability [5% Max]	0.005 mg
Permissible repeatability [5% Max]	0.012 mg
Linearity	±0.06 / 0.2 mg
Eccentric load deviation	0.2 mg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	3 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Analytical Balance, weighing pan, weighing pan shield, centring ring, bottom cover, brush, fabric dust cover, power supply.
Weighing chamber dimensions	168×160×228 mm
Weighing pan dimensions	ø90 mm open-work pan + ø85 mm (option) + ø68 mm (option) with pipette calibration adapter XA100-1 + ø36 mm (option) with pipette calibration adapter XA17-1
Packaging dimensions W x D x H	750×492×595 mm
Net weight	9.8 kg
Gross weight	14.3 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max; 9 – 17W*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3 °C / 1 h (±1 °C / 8 h)
Relative humidity	20% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Standard repeatability [5% Max] and **Standard minimum weight (USP)** are parameters obtained in automatic mode under special laboratory conditions.

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Power consumption depends on the terminal configuration as well as the number and type of external devices connected.

The power supply can be connected to the socket on the back of the balance housing or to the terminal.



Additional fee for verification



Accessories (Additional Fee)

MediaBox

RFID Tags

Antivibration Tables

Power Adapters

RS 232, RS 485 cables

Holders for laboratory flasks

Density determination KIT

Additional modules

Holders for test tubes and filters

Professional Weighing Tables

Protective cover for balances

Barcode scanners

Balance Storage Case

Automatic feeders

Label Printers

Adapters for Pipettes Calibration

THBR 2.0 System - Ambient Conditions Monitoring

MICRO-KIT - Set of Holders for Microscale Glassware

Under-pan weighing

Anti-Draft Chamber for XA 4Y and XA 5Y Balances

Weighing dishes

Antistatic ionizer

Receipt Printer

Fingerprint Reader

RS 232 – USB Converter

Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• Label Editor R02 [WX-010-0094]

• R-Lab [WX-010-0080]

• RADWAG Development Studio [WX-010-0104]

• RAD Key [WX-010-0005]

• RADWAG Remote Desktop [WX-010-0107]

• Scale Editor 2.1 [WX-010-0173]

Device dimensions W x D x H

