



More information on the website  
[mirror.radwag.com/en/info,w1,07Y](http://mirror.radwag.com/en/info,w1,07Y)

# MPS.M.5100/10000.R1 Weighing Module

WX-016-1002



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	5100 / 10000 g
Preload range	1000 g
Readability [d]	0.01 / 0.05 g
Repeatability	0.01 / 0.05 g
Linearity	±20 / 50 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	external
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	
Communication interface	RS232

### Electrical parameters

Power supply Adapter: 100 – 240V AC 50/60Hz 0.6A; 12V DC 1.2A Module: 12V DC

### Environmental conditions

Operating temperature +10 – +40 °C

Relative humidity 40% – 80%

### Physical parameters

Weighing pan dimensions  $\varnothing$ 100 mm

Device dimensions W x D x H 266x70x105 mm

Net weight 1.8 kg



## Accessories (Additional Fee)

RS 232, RS 485 cables  
Antivibration Tables

R Terminal (WDM-8)

## Software (Additional Fee)

• R-Panel [WX-010-0187]

# Device dimensions W x D x H

