



More information on the website
mirror.radwag.com/us/info,w1,ODB

MPS.M.3300.R1 Weighing Module

WX-016-0343



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]		3300 g
Preload range		330 g
Readability [d]		10 mg
Repeatability		7 mg
Linearity		±20 mg
Warm-up time after connection to power		1 h
Stabilization time		2 s
Adjustment		external
Construction		
Protection class		IP 43
Housing		aluminum
Weighing pan material		aluminum
Communication interface		
		RS232
Power supply		
		Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC

Operating temperature	+10 – +40 °C
-----------------------	--------------

Relative humidity	40% – 80%
-------------------	-----------

Physical parameters

Weighing pan dimensions	ø100 mm
-------------------------	---------

Device dimensions W x D x H	266x70x105 mm
-----------------------------	---------------

Net weight	1,8 kg
------------	--------



Accessories (Additional Fee)

RS 232, RS 485 cables
Antivibration tables

R Terminal (WDM-8)

Software (Additional Fee)

• R Panel [WX-010-0187]

Device dimensions W x D x H

