



More information on the website
mirror.radwag.com/us/info,w1,OG5

PM9600-SR433RBK20 Barcode Scanner

WX-006-0053



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Datalogic PowerScanPM9600is a quick and reliable scanner intended for area imager barcodes. The scanner ensures omnidirectional readout of barcodes, even from the distance of 1 m.

The PowerScan PM9600 cordless model further enhances the operator efficiency and safety with Datalogic's STAR Cordless System™. Bidirectional radio communication and display allow users to receive immediate feedback avoiding any risk of mistakes. A characteristic feature of the scanner is high resolution of the image sensor that meets expectations of most applications dedicated for warehouse, logistics, transport and production solutions.

Patented technology, the Green Spot and Datalogic 3GL™ (3 Green Lights), informs the user about correct barcode readout. This solution is ideal for rooms with high background noise such as industrial areas. The scanner is equipped with housing that features IP65/67 ingress protection which makes it both waterproof and dustproof device. Designed to withstand multiple drops from a height of 2 m to solid surface.

User comfort is guaranteed by ergonomic shape, i.e. handy and well-balanced design. These make DatalogicPM9600a perfect device to be applied in industry, logistics and warehouse.

Compatible with (Additional Fee)

MUYA Modules

HX7 H Multifunctional Scale
HX7.4N H Multifunctional Stainless Steel Ramp Scale
HX7.4C Multifunctional Platform Scale
HX7 HR Multifunctional Scale
XA 5Y.M.A.P Microbalance for pipettes calibration
WPY Multifunctional Scale
MYA 5Y.P Microbalance for pipettes calibration
C32 Multifunctional Scale
HY10.HRP.H High Resolution Scale
5Y.PM Precision balance
MYA 5Y.F Microbalance for Filters
HX7.4P2 H Multifunctional Stainless Steel Beam Scales
TMX H Stainless steel Multifunctional Scale
WLY Scales for PGC
AS X7 Analytical Balance
PS X7 Balances for PGC
TMX Multifunctional Scale
XA 5Y.M.A Microbalance
PS R2 Precision Balance
WLC X7 Precision balance
HX7.4N H.LD Multifunctional Stainless Steel Ramp Scale
CY10 Scales for PGC
DWT/RC/HYF Checkweighers
PUE CY10 Weighing Terminal
CY10 Multifunctional Scale
HX7.4P H Multifunctional Stainless Steel Pallet Scales
HY10 Multifunctional Scale
HY10 H Stainless Steel Multifunctional Scale
HY10.HRP High Resolution Scale
C32.PM Precision Balance
PUE 7.1.HRP High Resolution Scale
Automatic Balances for. Pipettes Calibration

HX7 Multifunctional Scale
HX7.4 H/Z Multifunctional Stainless Steel Platform Scale, pit version
PS X7 Precision Balance
WPY Scales for PGC
XA 5Y.A Analytical Balance
HX7.4 H Multifunctional Stainless Steel Platform Scale
HX7.4P2 Multifunctional Beam Scales
WAY 5Y.KO Manual Mass Comparator
AS 5Y Analytical Balance
PS 5Y Balances for PGC
PS R2.H Precision Balance
HY10.H scales for PGC
CY10 Precision balance
Analytical Balance for Filters XA 5Y.F
WLY Precision Balance
APP 5Y.KO Manual Mass Comparator
MYA 5Y Microbalance
PS R1 Precision Balance
XA 5Y Analytical Balance
5Y.PM.KB Manual Mass Comparator
AS R2 PLUS Analytical Balance
PUE C32 Weighing Terminal
PUE 7.1 Weighing Terminal
PUE HX7 Weighing Terminal
PUE 5 Weighing Terminal
PS 5Y Precision Balance
XA 5Y.KO Manual Mass Comparator
XA 5Y.M Microbalance
UYA 5Y.KO Manual Mass Comparator
AS R1 PLUS Analytical Balance
H315 H Waterproof Platform Scale
HX7.4P Multifunctional pallet scales
XA 5Y.M.A.S Microbalance for stents weighing