



More information on the website
mirror.radwag.com/en/info,w1,0S6

XA 53.5Y.M.A Microbalance

WL-109-0018



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- | | | | |
|---|---|---|--|
|  Autotest |  Dosing |  Percent Weighing |  Parts counting |
|  Peak hold |  Formulation |  Newton unit measurement |  Statistics |
|  Checkweighing |  IR sensors |  GLP Procedures |  Animal weighing |
|  Pipettes Calibration |  Air density correction |  Automatic sliding door |  Density determination |
|  Differential weighing |  Ambient conditions monitoring |  Statistical Quality Control |  Packaged Goods Control |
|  ALIBI Memory |  Wi-Fi | | |

Datasheet

Metrological parameters

Maximum capacity [Max]	53 g
Minimum load	0.1 mg

Metrological parameters	
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-53 g
Standard repeatability [5% Max]	0.7 µg
Standard minimum weight (USP)	1.4 mg
Standard minimum weight (U=1%, k=2)	0.3 mg
Permissible repeatability [5% Max]	2.4 µg
Permissible repeatability [Max]	8 µg
Linearity	±20 µg
Eccentric load deviation	20 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	~ 3.5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, weighing pan, weighing pan shield, power supply, brush, fabric dust cover.
Weighing chamber dimensions	199×170×217 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	14.5 kg
Gross weight	20 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Standard repeatability [5% Max] and **Standard minimum weight (USP)** are parameters obtained in automatic mode under special laboratory conditions.

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories (Additional Fee)

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
Protective cover for balances
RS 232, RS 485 cables
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Barcode scanners
Automatic feeders

MICRO-KIT - Set of Holders for Microscale Glassware
Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
Adapters for Pipettes Calibration
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Weighing dishes
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions W x D x H

