



More information on the website
mirror.radwag.com/en/info,w1,PDS

PL/300/H6 Platform

WX-009-0022



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|--------------------------------|-------------------------|
| Maximum capacity [Max] | 300 kg |
| Readability [d] | 100 g |
| Construction | |
| Protection class | IP 66 / 67 |
| Construction | Stainless steel AISI304 |
| Weighing pan material | Stainless steel AISI304 |
| Physical parameters | |
| Weighing pan dimensions | 800×800 mm |
| Packaging dimensions W x D x H | 1250×820×270 mm |

Readability accuracy – expected value, dependent on the parameters of the measuring transmitter used.



Accessories (Additional Fee)

PUE 5 Weighing Terminal
 PUE HX7 Weighing Terminal
 PUE 7.1 Weighing Terminal

PUE C315 Weighing Terminal
 PUE HY10 Weighing Terminal
 PUE H315 Weighing Terminal

Device dimensions W x D x H




PL/D2



PLC/F1



PLC/C2
PLC/C3



PL/H
PL/HR

| Platform type | A1 | A2 | H |
|---------------------|-----|-----|-------|
| PL/D2 | 238 | 216 | 82±3 |
| PLC/F1 | 300 | 300 | 70±3 |
| PLC/C2 | 402 | 502 | 103±3 |
| PLC/C3 | 701 | 501 | 130±5 |
| PL/H1 / PL/HR1 | 150 | 200 | 85±3 |
| PL/H2 / PL/HR2 | 250 | 300 | 103±3 |
| PL/H3 / PL/HR/3 | 410 | 410 | 98±3 |
| PL/H3/5 / PL/HR/3/5 | 400 | 600 | 155±3 |
| PL/H4 / PL/HR/4 | 500 | 500 | 155±3 |
| PL/H5 / PL/HR/5 | 600 | 600 | 155±3 |
| PL/H6 | 800 | 800 | 135±3 |

dimensions in mm