



More information on the website  
[mirror.radwag.com/en/info,w1,PGF](http://mirror.radwag.com/en/info,w1,PGF)

# PLC/150/C3 Platform

WX-009-0007



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	150 kg
Readability [d]	50 g
Construction	
Protection class	IP 65
Construction	mild steel St3S
Weighing pan material	Stainless steel AISI304
Physical parameters	
Weighing pan dimensions	500×700 mm
Packaging dimensions W x D x H	730×800×270 mm

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.




## Accessories (Additional Fee)


CY10 Scales for PGC  
 PUE CY10 Weighing Terminal  
 CY10 Multifunctional Scale  
 PUE 5 Weighing Terminal  
 CY10 Precision Balance  
 PUE HX7 Weighing Terminal

PUE C32 Weighing Terminal  
 PUE 7.1 Weighing Terminal  
 PUE C315 Weighing Terminal  
 PUE HY10 Weighing Terminal  
 PUE H315 Weighing Terminal


## Device dimensions W x D x H





PL/D2



PLC/F1



PLC/C2  
PLC/C3



PL/H  
PL/HR

Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR/3	410	410	98±3
PL/H3/5 / PL/HR/3/5	400	600	155±3
PL/H4 / PL/HR/4	500	500	155±3
PL/H5 / PL/HR/5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm