



More information on the website
mirror.radwag.com/en/info,w1,PGF

PLC/150/C3 Platform

WX-009-0007



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	150 kg
Readability [d]	50 g
Construction	
Protection class	IP 65
Construction	mild steel St3S
Weighing pan material	Stainless steel AISI304
Physical parameters	
Weighing pan dimensions	500×700 mm
Packaging dimensions W x D x H	730×800×270 mm

Readability accuracy – expected value, dependent on the parameters of the measuring transmitter used.



Accessories (Additional Fee)

CY10 Scales for PGC
 PUE CY10 Weighing Terminal
 CY10 Multifunctional Scale
 PUE 5 Weighing Terminal
 CY10 Precision Balance
 PUE HX7 Weighing Terminal

PUE C32 Weighing Terminal
 PUE 7.1 Weighing Terminal
 PUE C315 Weighing Terminal
 PUE HY10 Weighing Terminal
 PUE H315 Weighing Terminal

Device dimensions W x D x H



PL/D2



PLC/F1



PLC/C2
PLC/C3



PL/H
PL/HR



Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR/3	410	410	98±3
PL/H3/5 / PL/HR/3/5	400	600	155±3
PL/H4 / PL/HR/4	500	500	155±3
PL/H5 / PL/HR/5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm