



More information on the website  
[mirror.radwag.com/us/info,w1,PI3](https://mirror.radwag.com/us/info,w1,PI3)

# HX7.4N.600.H3 Multifunctional Stainless Steel Ramp Scale

WP-227-0009



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Formulation



Replaceable unit



ALIBI Memory

## Datasheet

| Metrological parameters                |         |
|----------------------------------------|---------|
| Maximum capacity [Max]                 | 600 kg  |
| Minimum load                           | 4 kg    |
| Readability [d]                        | 200 g   |
| Verification unit [e]                  | 200 g   |
| Tare range                             | -600 kg |
| Max readability for non-verified scale | 100 g   |
| OIML Class                             | III     |

| Physical parameters            |                                                                                                                     |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Display                        | 7" graphic colour                                                                                                   |
| Cable length                   | 3 m                                                                                                                 |
| Weighing pan dimensions        | 1200×1500 mm                                                                                                        |
| Packaging dimensions W x D x H | 1600×1600×500 mm                                                                                                    |
| Net weight                     | 179,7 kg                                                                                                            |
| Gross weight                   | 221,3 kg                                                                                                            |
| Construction                   |                                                                                                                     |
| Protection class               | IP 66 / 69 construction, IP 66 / 67 terminal                                                                        |
| Keypad                         | membrane                                                                                                            |
| Construction                   | Stainless steel AISI304                                                                                             |
| Communication interface        |                                                                                                                     |
| Communication interface        | RS232, USB-A, 4IN, 4OUT, Ethernet, Modbus TCP/IP                                                                    |
| Optional interfaces            | USB (M12 4P), RS485, RS232, Profibus (Dp SLAVE), PROFINET (RJ45), EtherNet/IP (RJ45), 12 IN / 12 OUT, 4-20mA, 0-10V |
| Electrical parameters          |                                                                                                                     |
| Power supply                   | 100 – 240 V AC 50/60 Hz                                                                                             |
| Power consumption max.         | 25 W                                                                                                                |
| Optional power supply          | 12 – 24 V DC                                                                                                        |
| Environmental conditions       |                                                                                                                     |
| Operating temperature          | -10 – +40 °C                                                                                                        |
| Storage temperature            | -10 – +50 °C                                                                                                        |
| Relative humidity              | 10% – 80% RH no condensation                                                                                        |
| Indicator                      | PUE HX7                                                                                                             |
| Number of buttons              | 22                                                                                                                  |
| Features of use                |                                                                                                                     |
| Max number of platforms        | 2                                                                                                                   |



Additional fee for verification



## Accessories (Additional Fee)

RS 232 cables (scale - printer)  
 RS 232 cables (scale - ZEBRA printer)  
 Displays  
 Power Adapters  
 RS 232, RS 485 cables  
 USB cable (scale - printer)  
 IN/OUT Cables  
 Barcode scanners


Label Printers  
 Stands, wall mounting kits and mounting brackets  
 Keypad, external switches  
 USB adapter  
 Receipt Printer  
 Additional Weighing platforms Module  
 RS 232 – USB Converter  
 Additional modules

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

# Device dimensions W x D x H



| Model          | Max     | A    | B    | C    | C1 | D    | E    | F    | G    | H    |
|----------------|---------|------|------|------|----|------|------|------|------|------|
| HX7.4N.150.H1  | 150 kg  | 840  | 860  | 45,5 | 76 | 1040 | 1710 | 778  | 940  | 1170 |
| HX7.4N.300.H1  | 300 kg  | 840  | 860  | 45,5 | 76 | 1040 | 1710 | 778  | 940  | 1170 |
| HX7.4N.600.H1  | 600 kg  | 840  | 860  | 45,5 | 76 | 1040 | 1710 | 778  | 940  | 1170 |
| HX7.4N.150.H2  | 1500 kg | 1100 | 1200 | 45,5 | 76 | 1300 | 2050 | 1118 | 1200 | 1430 |
| HX7.4N.300.H2  | 300 kg  | 1100 | 1200 | 45,5 | 76 | 1300 | 2050 | 1118 | 1200 | 1430 |
| HX7.4N.600.H2  | 600 kg  | 1100 | 1200 | 45,5 | 76 | 1300 | 2050 | 1118 | 1200 | 1430 |
| HX7.4N.1500.H2 | 1500 kg | 1100 | 1200 | 52,5 | 76 | 1300 | 2150 | 1118 | 1200 | 1430 |
| HX7.4N.300.H3  | 300 kg  | 1200 | 1500 | 45,5 | 76 | 1400 | 2350 | 1418 | 1300 | 1530 |
| HX7.4N.600.H3  | 600 kg  | 1200 | 1500 | 45,5 | 76 | 1400 | 2350 | 1418 | 1300 | 1530 |
| HX7.4N.1500.H3 | 1500 kg | 1200 | 1500 | 52,5 | 76 | 1400 | 2450 | 1418 | 1300 | 1530 |
| HX7.4N.300.H4  | 300 kg  | 1500 | 1500 | 52,5 | 76 | 1700 | 2450 | 1418 | 1600 | 1830 |
| HX7.4N.600.H4  | 600 kg  | 1500 | 1500 | 52,5 | 76 | 1700 | 2450 | 1418 | 1600 | 1830 |
| HX7.4N.1500.H4 | 1500 kg | 1500 | 1500 | 52,5 | 76 | 1700 | 2450 | 1418 | 1600 | 1830 |

\* dimensions in mm