



More information on the website  
[mirror.radwag.com/us/info,w1,Q67](https://mirror.radwag.com/us/info,w1,Q67)

# WTC 200 Precision Balance

WL-210-0004



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Plus/Minus Control



Percent Weighing



Parts counting



Peak hold



GLP Procedures



ALIBI Memory

## Datasheet

| Maximum capacity [Max] | 200 g    |
|------------------------|----------|
| Readability [d]        | 0,001 g  |
| Tare range             | -200 g   |
| Repeatability          | 0,002 g  |
| Linearity              | ±0,004 g |
| Stabilization time     | 2 s      |
| Adjustment             | external |
| Physical parameters    |          |
| Leveling system        | manual   |

| Physical parameters            |                                                                                  |
|--------------------------------|----------------------------------------------------------------------------------|
| Display                        | 4,3" LCD (backlit)                                                               |
| Weighing pan dimensions        | ø100 mm                                                                          |
| Packaging dimensions W x D x H | 330×230×140 mm                                                                   |
| Net weight                     | 0,96 kg                                                                          |
| Gross weight                   | 1 kg                                                                             |
| Construction                   |                                                                                  |
| Protection class               | IP 43                                                                            |
| Communication interface        | RS232, USB-A, USB-B                                                              |
| Power supply                   | Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A<br>Balance: 10 – 15VDC 0,6A max |
| Operation time on batteries    | 15 h (average time)                                                              |
| Operating temperature          | +15 – +30 °C                                                                     |
| Relative humidity              | 10% – 85% RH no condensation                                                     |



## Accessories (Additional Fee)

Antivibration tables  
Power Adapters  
RS 232 cables (scale - printer)  
Cigarette lighter receptacle power supply cables



Displays  
RS 232, RS 485 cables  
Receipt Printer

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- Alibi Reader PC Software [WX-010-0114]

## Device dimensions W x D x H



WTC, d = 0.001 g