



More information on the website  
[mirror.radwag.com/en/info,w1,QJJ](https://mirror.radwag.com/en/info,w1,QJJ)

# HX5.EX-1.4.1500.H10 4 Load Cell Platform Scale

WW-009-0023



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

| Metrological parameters |          |
|-------------------------|----------|
| Maximum capacity [Max]  | 1500 kg  |
| Minimum load            | 10 kg    |
| Readability [d]         | 500 g    |
| Verification unit [e]   | 500 g    |
| Tare range              | -1500 kg |
| OIML Class              | III      |

| Physical parameters      |   |
|--------------------------|---|
| Display                  | 5" graphic colour                                   |
| Cable length             | 3 m   |
| Weighing pan dimensions  | 1500×2000 mm  |
| Net weight               | 287.8 kg  |
| Gross weight             | 288 kg  |
| Construction             |   |
| Protection class         | IP 66 / 69 construction, IP 66 / 68 terminal        |
| ATEX Certification       | II 2G Ex ib IIC T4 Gb<br>II 2D Ex ib IIIC T135°C Db |
| IECEX Certification      | Ex ib IIC T4 Gb<br>Ex ib IIIC T135°C Db             |
| Construction             | Stainless steel AISI304                             |
| Communication interface  |   |
| Communication interface  | 2×RS232, RS485                                      |
| Electrical parameters    |   |
| Power supply             | 100 – 240 V AC 50/60 Hz                             |
| Power consumption max.   | 15 W  |
| Environmental conditions |   |
| Operating temperature    | -10 – +40 °C  |
| Relative humidity        | 10% – 85% RH no condensation                        |
| Indicator                | PUE HX5.EX-1  |



Additional fee for verification



## Accessories (Additional Fee)

Communication Modules  
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
Weighing Terminal

Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]