



More information on the website  
[mirror.radwag.com/ja/info,w1,QM0](http://mirror.radwag.com/ja/info,w1,QM0)

# AS 160.R2 PLUS分析天秤

WL-104-0176



The drawings, photos and graphics used are for illustrative purposes only.

## 機能



Autotest



Dosing



Percent Weighing



Totalizing



Parts counting



Peak hold



Newton unit  
measurement



Statistics



Checkweighing



Under-pan weighing



GLP Procedures



Animal weighing



Density determination

## データシート

### 計測パラメータ

最大ひょう量 [Max]	160 g
最小荷重	10 mg
最小表示 [d]	0,1 mg
法定計量時の単位 [e]	1 mg
風袋範囲	-160 g
標準最小計量値 (USP)	140 mg

計測パラメータ	
標準最小計量値 (U=1%, k=2)	14 mg
標準繰り返し性 [Max]	0,08 mg
標準繰り返し性 [5% Max]	0,07 mg
許容繰り返し性 [Max]	0,1 mg
許容繰り返し性 [5% Max]	0,09 mg
直線性	±0,2 mg
安定化時間	2 s
調整	内部 (自動)
OIMLクラス	I
物理的パラメータ	
レベリングシステム	手動
ディスプレイ	5,3" LCD (バックライト付き)
計量室のドア	手動
納品構成	バランス, 計量皿, 計量皿用シールド, センタリングリング, ボトムカバー, 電源.
計量皿寸法	ø100 mm
梱包寸法 幅x奥行x高さ	490x400x520 mm
正味重量	6,95 kg
総重量	9 kg
工事中	
保護クラス	IP 43
通信インターフェース	
通信インターフェース	2xRS232 <sup>1</sup> , 2xUSB-A (交換可能), USB-B, Wi-Fi (オプション)
電気的パラメータ	
消費電力 max.	3 W
過電圧保護	はい
環境条件	
動作温度	+10 – +40 °C
相対湿度	40% – 80%

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



## アクセサリ (Additional Fee)

防振台  
 実験用フラスコホルダー  
 電源アダプタ  
 シガーライターソケット電源ケーブル  
 粒状体密度測定キット  
 USB cable (はかり - プリンタ)  
 プロ仕様の計量テーブル

ピペット校正用ワークステーション  
 RS 232、RS 485 ケーブル  
 ディスプレイ  
 天秤用保護カバー  
 計量皿  
 静電気防止イオナイザ (除電器)  
 レシートプリンタ

## ソフトウェア (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]
- R-Panel [WX-010-0187]
- R-Lab [WX-010-0080]

## デバイスの寸法 幅x奥行x高さ

