



More information on the website  
[mirror.radwag.com/en/info,w1,QOS](http://mirror.radwag.com/en/info,w1,QOS)

# PLC/60/C2 Platform

WX-009-0004



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	60 kg
Readability [d]	20 g
Construction	
Protection class	IP 65
Construction	mild steel St3S
Weighing pan material	Stainless steel AISI304
Physical parameters	
Weighing pan dimensions	400×500 mm
Packaging dimensions	720×620×210 mm

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.



## Accessories (Additional Fee)


CY10 Scales for PGC  
 PUE CY10 Weighing Terminal  
 CY10 Multifunctional Scale  
 PUE 5 Weighing Terminal  
 CY10 Precision Balance  
 PUE C32 Weighing Terminal

PUE 7.1 Weighing Terminal  
 PUE HX7 Weighing Terminal  
 PUE C315 Weighing Terminal  
 PUE HY10 Weighing Terminal  
 PUE H315 Weighing Terminal


## Device dimensions




PL/D2




PLC/F1



PLC/C2  
PLC/C3



PL/H  
PL/HR



Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR3	410	410	98±3
PL/H3/5 / PL/HR3/5	400	600	155±3
PL/H4 / PL/HR4	500	500	155±3
PL/H5 / PL/HR5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm