



C32.120.PM Precision Balance

WL-223-0082

More information on the website
mirror.radwag.com/us/info,w1,QTM



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



IR sensors



GLP Procedures



Animal weighing



Density determination



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	120 kg
Minimum load	-
Preload range	12 kg
Readability [d]	0,2 g
Tare range	-120 kg
Minimum weight (USP)	164 g

Metrological parameters	
Minimum weight (U=1%, k=2)	16,4 g
Repeatability (Max)	0,2 g
Repeatability (5% Max)	0,082 g
Linearity	±0,6 g
Stabilization time	1 s
Adjustment	internal (automatic)
Physical parameters	
Leveling system	manual
Display	5" graphic colour
Weighing pan dimensions	400×500 mm
Packaging dimensions W x D x H	710×610×240 mm
Net weight	22 kg
Gross weight	24,5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Balance: 10 – 12V DC 1A max
Environmental conditions	
Operating temperature	+10 – +40 °C

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

Displays
 Antivibration tables
 Power Adapters
 RS 232 cables (scale - printer)
 Cigarette lighter receptacle power supply cables
 Professional Weighing Tables

Barcode scanners
 RS 232, RS 485 cables
 Stands, wall mounting kits and mounting brackets
 Receipt Printer
 AP2-1 Current Loop Unit

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Alibi Reader PC Software [WX-010-0114]

- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions W x D x H

