




More information on the website
mirror.radwag.com/en/info,w1,QUA29

AKM-2.20.5Y Automatic Mass Comparators

WL-411-0013



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
E1 Calibration Range	5 – 20 kg
E2 Calibration Range	1 – 20 kg
F1 Calibration Range	1 – 20 kg
F2 Calibration Range	1 – 20 kg
Maximum capacity [Max]	20.5 kg
Readability [d]	0.1 mg
Standard repeatability [5% Max]	0.15 mg
Standard repeatability [Max]	0.2 mg
Permissible repeatability	0.3 mg
Eccentricity (tested load)	0 mg
Electric compensation range	-500 g – +500 g
Stabilization time	30 s
Adjustment	external (500g)

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	ø190 mm - self centering
Weighing device dimensions	1150×770×1300 mm
Controlling device dimensions	249×170×72 mm
Packaging dimensions	1150×770×1300 mm
Net weight	235 kg
Net weight	235 kg
Gross weight	352 kg
Gross weight	352 kg
Supplementary weights internal	automatic
Supplementary weights external	-

Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot

Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz

Environmental conditions	
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0.5 °C / 12 h (±0.3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (3% / 4 h)

Repeatability is expressed as a standard deviation determined for 6 ABBA cycles. Standard deviation is experimentally determined under ambient conditions for calibration of E1 class mass standards specified in OIML R111 (Table C.1.) document.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

RFID Tags
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables



THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software (Additional Fee)

• RAD Key [WX-010-0005]
 • RMCS System Network Management of Calibration Process [WX-010-0048]

• RMCS Lite [WX-010-0164]

Device dimensions



AKM-2