



More information on the website
mirror.radwag.com/en/info,w1,QWZ

C315.15/30.C3.M Load Cell Platform Scale

WP-123-1022



The drawings, photos and graphics used are for illustrative purposes only.

Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	15 / 30 kg
Minimum load	100 g
Readability [d]	5 / 10 g
Verification unit [e]	5 / 10 g
Tare range	-30 kg
OIML Class	III

Physical parameters		
Display		4.3" LCD (backlit)
Weighing pan dimensions		500×700 mm
Packaging dimensions W x D x H		730×800×270 mm
Net weight		23.4 kg
Gross weight		27.2 kg
Construction		
Protection class		IP 65 construction, IP 43 terminal
Construction		mild steel St3S
Weighing pan material		Stainless steel AISI304
Communication interface		
Communication interface		RS232
Optional interfaces		RS232
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz and battery
Power consumption max.		5 W
Operation time on batteries		max 8h
Environmental conditions		
Operating temperature		-10 – +40 °C
Storage temperature		-10 – +50 °C
Relative humidity		10% – 85% RH no condensation
Indicator		C315



Additional fee for verification



Accessories (Additional Fee)

Power Adapters

RS 232 cables (scale - printer)

Cigarette lighter receptacle power supply cables

Displays

RS 232, RS 485 cables

RS 232 – Ethernet Converter

AP2-1 Current Loop Unit

RS 232 – USB Converter

RS 232 – RS 485 Converter

Receipt Printer

Stands, wall mounting kits and mounting brackets

Software (Additional Fee)

• RAD Key [WX-010-0005]

• Scale Editor 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

Device dimensions W x D x H

