



More information on the website  
[mirror.radwag.com/en/info,w1,R26](http://mirror.radwag.com/en/info,w1,R26)

# C315.4P2.2000.C1 Beam Scale

WP-240-0002



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

## Datasheet

| Metrological parameters |          |
|-------------------------|----------|
| Maximum capacity [Max]  | 2000 kg  |
| Minimum load            | 20 kg    |
| Readability [d]         | 1 kg     |
| Verification unit [e]   | 1 kg     |
| Tare range              | -2000 kg |
| OIML Class              | III      |

| Physical parameters         |  |
|-----------------------------|--|
| Display                     | 4.3" LCD (backlit)                             |
| Cable length                | 3 m + 5 m                                      |
| Weighing pan dimensions     | 2 pcs 2 m                                      |
| Device dimensions W x D x H | 2000×120×105 mm                                |
| Scale mass with indicator   | 53 kg  |
| Construction                |  |
| Protection class            | IP 65 construction, IP 67 cell, IP 43 terminal |
| Communication interface     |  |
| Communication interface     | RS232  |
| Optional interfaces         | RS232  |
| Electrical parameters       |  |
| Power supply                | 100 – 240 V AC 50/60 Hz and battery            |
| Power consumption max.      | 5 W  |
| Operation time on batteries | max 8h   |
| Environmental conditions    |  |
| Operating temperature       | -10 – +40 °C                                   |
| Relative humidity           | 10% – 85% RH no condensation                   |



Additional fee for verification



## Accessories (Additional Fee)

Power Adapters

RS 232 cables (scale - printer)

Stands, wall mounting kits and mounting brackets

Cigarette lighter receptacle power supply cables

Displays

RS 232 – Ethernet Converter

AP2-1 Current Loop Unit

RS 232, RS 485 cables

RS 232 – USB Converter

RS 232 – RS 485 Converter

Receipt Printer


## Software (Additional Fee)

• RAD Key [WX-010-0005]

• Scale Editor 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

## Device dimensions W x D x H



| Scale type       | A   | B    | H   | D    |
|------------------|-----|------|-----|------|
| C315.4P2.600.C   | 120 | 1200 | 85  | 1100 |
| C315.4P2.1500.C  | 120 | 1200 | 85  | 1100 |
| C315.4P2.3000.C  | 120 | 1200 | 85  | 1100 |
| C315.4P2.2000.C1 | 120 | 2000 | 105 | 1900 |
| C315.4P2.2000.C2 | 120 | 2500 | 105 | 2400 |
| C315.4P2.4000.C1 | 120 | 2000 | 155 | 1880 |
| C315.4P2.4000.C2 | 120 | 2500 | 155 | 2380 |
| C315.4P2.6000.C1 | 120 | 2000 | 155 | 1880 |
| C315.4P2.6000.C2 | 120 | 2500 | 155 | 2380 |

dimensions in mm