



More information on the website
mirror.radwag.com/en/info,w1,R80

C315.30/60.C2.K Load Cell Platform Scale

WP-123-1014



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit
measurement



GLP Procedures



Animal weighing



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	30 / 60 kg
Minimum load	200 g
Readability [d]	10 / 20 g
Verification unit [e]	10 / 20 g
Tare range	-60 kg
OIML Class	III

Physical parameters		
Display		4.3" LCD (backlit)
Cable length		2.5 m
Weighing pan dimensions		400×500 mm
Packaging dimensions W x D x H		720×620×210 mm
Net weight		12.5 kg
Gross weight		15 kg
Construction		
Protection class		IP 65 construction, IP 43 terminal
Construction		mild steel St3S
Weighing pan material		Stainless steel AISI304
Communication interface		
Communication interface		RS232
Optional interfaces		RS232
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz and battery
Power consumption max.		5 W
Operation time on batteries		max 8h
Environmental conditions		
Operating temperature		-10 – +40 °C
Storage temperature		-10 – +50 °C
Relative humidity		10% – 85% RH no condensation
Indicator		C315



Additional fee for verification



Accessories (Additional Fee)



Antivibration Tables
Power Adapters
RS 232 cables (scale - printer)
Stands, wall mounting kits and mounting brackets
Cigarette lighter receptacle power supply cables
Displays

RS 232, RS 485 cables
RS 232 – Ethernet Converter
AP2-1 Current Loop Unit
RS 232 – USB Converter
RS 232 – RS 485 Converter
Receipt Printer


Software (Additional Fee)

• RAD Key [WX-010-0005]
• Scale Editor 2.1 [WX-010-0173]



• R-Lab [WX-010-0080]




C315.F1.M



C315.F1.R




C315.C2.M




C315.C2.K



Device dimensions W x D x H





C315.C2.R



C315.C2.K



C315.C3.M



C315.C3.K