



More information on the website
mirror.radwag.com/en/info,w1,RBW

DWM Checkweigher

WK-105-000_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	750 – 7500 g
Readability [d]	0.1 – 5 g
Verification unit [e]	0.1 – 5 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	Stainless steel / aluminum anodised
Communication interface	
Communication interface	Ethernet, USB, RS232, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions	
Operating temperature	+5 – +40 °C
Components and software	
Operating system	Microsoft Windows 11 IoT
Features of use	
Capacity	max 500 pcs/min
Conveyor velocity	1.6 m/s

*OIML class for checkweighers used in packaged goods control (PGC) systems.



Accessories (Additional Fee)

RS 232 cables (scale - ZEBRA printer)
 RS 232, RS 485 cables
 Label Printers
 Tunnel Detectors

USB adapter
 Receipt Printer
 USB cable (scale - printer)