



More information on the website
mirror.radwag.com/en/info,w1,RBW

DWM Checkweigher

WK-105-0005



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|-------------------------|--------------------------------|
| Maximum capacity [Max] | 7500 g |
| Readability [d] | 0.1 g |
| Tare range | -7500 g |
| OIML Class | XIII (1), Y (a) |
| Physical parameters | |
| Display | 12" graphic colour touchscreen |
| Construction | |
| Protection class | IP 55, IP 65 |
| Keypad | touch screen |
| Construction | mild steel / Stainless steel |
| Communication interface | |
| Communication interface | Ethernet, USB, RS232, I / O |

Environmental conditions

Operating temperature +5 – +40 °C

Features of use

Capacity max 500 pcs/min



Accessories (Additional Fee)

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Label Printers

Tunnel Detectors

USB adapter

Receipt Printer

USB cable (scale - printer)