



More information on the website
mirror.radwag.com/us/info,w1,RBW

DWM Checkweigher

WK-105-000_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	750 – 7500 g
Readability [d]	0,1 – 5 g
Verification unit [e]	0,1 – 5 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	Stainless steel / aluminum anodised
Communication interface	
Communication interface	Ethernet, USB, RS232, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions

Operating temperature +5 – +40 °C

Components and software

Operating system Microsoft Windows 11 IoT

Features of use

Capacity max 500 pcs/min

Conveyor velocity 1,6 m/s



Accessories (Additional Fee)

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Label Printers

Tunnel detectors

USB adapter

Receipt Printer

USB cable (scale - printer)