



XA 200.5Y.KO Mass Comparator

WL-405-0023

More information on the website
mirror.radwag.com/en/info,w1,RUB



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Automatic sliding door

Datasheet

Metrological parameters	
E1 Calibration Range	200 g
E2 Calibration Range	50 g – 200 g
F1 Calibration Range	50 mg – 200 g
F2 Calibration Range	1 mg – 200 g
M1 Calibration Range	1 mg – 200 g
M2 Calibration Range	1 mg – 200 g
Maximum capacity [Max]	210 g
Readability [d]	0.01 mg
Standard repeatability [5% Max]	0.005 mg
Standard repeatability [Max]	0.025 mg
Permissible repeatability	0.05 mg

Metrological parameters	
Linearity	±0.2 mg
Eccentricity (tested load)	1d / 1 mm
Electric compensation range	0 – +210 g
Stabilization time	5 s
Adjustment	internal (automatic)

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	Ø90 mm
Weighing device dimensions	564x253x300 mm
Controlling device dimensions	249x170x72 mm
Packaging dimensions W x D x H	765x515x545 mm
Net weight	15.7 kg
Gross weight	20.1 kg

Communication interface	
Communication interface	2xUSB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot

Environmental conditions	
Operating temperature	+15 – +35 °C
Operating temperature change rate	±1 °C / 12 h
Relative humidity	40% – 70%
Relative humidity change rate	±5% / 4 h

Repeatability is expressed as a standard deviation determined for 6 ABBA cycles. Standard deviation is experimentally determined under ambient conditions for calibration of F2 class mass standards specified in OIML R111 (Table C.1.) document.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

RFID Tags
Antivibration Tables
Additional modules
Protective cover for balances
Barcode scanners
RS 232, RS 485 cables
Label Printers

THBR 2.0 System - Ambient Conditions Monitoring
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Receipt Printer
Fingerprint Reader
RS 232, RS 485 cables
RS 232 cables (scale - printer)

Software (Additional Fee)

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]
- RMCS Lite [WX-010-0164]