



More information on the website
mirror.radwag.com/en/info,w1,S8Z

C315.15/30.F1.M Load Cell Platform Scale

WP-123-1007



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit
measurement



GLP Procedures



Animal weighing



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	15 / 30 kg
Minimum load	100 g
Readability [d]	5 / 10 g
Verification unit [e]	5 / 10 g
Tare range	-30 kg
OIML Class	III

Physical parameters		
Display		4.3" LCD (backlit)
Weighing pan dimensions		300×300 mm
Packaging dimensions W x D x H		570×390×170 mm
Net weight		5.3 kg
Gross weight		6.6 kg
Construction		
Protection class		IP 65 construction, IP 43 terminal
Construction		mild steel St3S
Weighing pan material		Stainless steel AISI304
Communication interface		
Communication interface		RS232
Optional interfaces		RS232
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz and battery
Power consumption max.		5 W
Operation time on batteries		max 8h
Environmental conditions		
Operating temperature		-10 – +40 °C
Storage temperature		-10 – +50 °C
Relative humidity		10% – 85% RH no condensation
Indicator		C315



Additional fee for verification



Accessories (Additional Fee)

Antivibration Tables
Power Adapters
RS 232 cables (scale - printer)
Cigarette lighter receptacle power supply cables
Displays
RS 232, RS 485 cables

RS 232 – Ethernet Converter
AP2-1 Current Loop Unit
RS 232 – USB Converter
RS 232 – RS 485 Converter
Receipt Printer
Stands, wall mounting kits and mounting brackets

Software (Additional Fee)

• RAD Key [WX-010-0005]
• Scale Editor 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

Device dimensions W x D x H

