



More information on the website
mirror.radwag.com/us/info,w1,S9H

DWT/RC SY Checkweigher

WK-106-____



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	10 – 600 kg
Minimum load	0,1 – 4 kg
Readability [d]	5 – 200 g
Tare range	-10 – -600 kg
Physical parameters	
Display	10,1" graphic colour touchscreen
Construction	
Protection class	IP 55
Communication interface	RS232, RS485
Operating temperature	-10 – +40 °C
Features of use	
Capacity	max 50 pcs/min
Conveyor velocity	0,1 – 0,5 m/s



Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]