



More information on the website
mirror.radwag.com/us/info,w1,S9H

DWT/RC SY Checkweigher

WK-106-002_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|-------------------------|---|
| Maximum capacity [Max] | 15 – 60 kg |
| Readability [d] | 5 – 20 g |
| Verification unit [e] | 5 – 20 g |
| OIML Class | XIII (1)*, Y (a) |
| Physical parameters | |
| Display | 10,1" graphic colour touchscreen |
| Construction | |
| Protection class | IP 55 |
| Keypad | touch screen |
| Construction | mild steel |
| Communication interface | |
| Communication interface | RS232, RS485, Ethernet, USB, IN/OUT |
| Optional interfaces | Profibus, Profinet, EtherNet/IP, Modbus |

| Environmental conditions | |
|--------------------------|-----------------|
| Operating temperature | -10 – +40 °C |
| Components and software | |
| Operating system | Linux |
| Features of use | |
| Capacity | max 100 pcs/min |
| Conveyor velocity | 0,1 – 1,7 m/s |



Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

!Keypad, external switches

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]