



More information on the website
mirror.radwag.com/us/info,w1,SUY

MA 110.R.WH Moisture Analyzer

WL-305-0007



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Statistics



GLP Procedures



Replaceable unit



Statistical Quality Control



ALIBI Memory



Drying modes



Samples drying



Moisture content analysis



Dry mass determination

Datasheet

Metrological parameters	
Maximum capacity [Max]	110 g
Readability [d]	1 mg
Tare range	-110 g
Adjustment	external
Maximum sample weight	110 g
Heating module	halogen
Moisture content repeatability	±0,05 % (sample ~ 2 g), ±0,01 % (sample ~ 10 g)

Metrological parameters	
Moisture content readability	0,001 %
Drying temperature range	Max 250 °C
Physical parameters	
Leveling system	manual
Display	5,3" LCD (backlit)
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions W x D x H	476×381×346 mm
Net weight	4,8 kg
Gross weight	6 kg
Construction	
Protection class	IP 43
Features of use	
Display mode	%D, %M, %R, g
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
Communication interface	
Communication interface	RS232 ¹ , USB-A, USB-B, Wi-Fi
Electrical parameters	
Power supply	100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz
Power consumption	4 W
Heating module power	450 W
Environmental conditions	
Operating temperature	+10 – +40 °C
Mass indication control	External mass standard 50g, 100g, 200g, depending on the type of moisture analyzer (additional equipment)
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)
Drying temperature control	One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set (additional equipment)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

Antivibration tables
Moisture analyzer accessories
Barcode scanners

Receipt Printer
RS 232, RS 485 cables
RS 232 cables (scale - printer)

Software (Additional Fee)

• RAD Key [WX-010-0005]

• RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

