



More information on the website
mirror.radwag.com/us/info,w1,T03

MPS.M.640.R1 Weighing Module

WX-016-0341



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	640 g
Preload range	64 g
Readability [d]	1 mg
Repeatability	0,8 mg
Linearity	±2 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	external
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	RS232, max 115,2 kbps, Radwag ASCII protokół
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Moduł: 12V DC

Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
Physical parameters	
Weighing pan dimensions	ø40 mm
Device dimensions W x D x H	220x70x100 mm
Net weight	1,8 kg



Accessories (Additional Fee)

RS 232, RS 485 cables

RS 232, RS 485 cables

Software (Additional Fee)

• R Panel [WX-010-0187]

Device dimensions W x D x H

