



More information on the website  
[mirror.radwag.com/en/info,w1,TDO](http://mirror.radwag.com/en/info,w1,TDO)

# DWT/RC HP Checkweigher

WK-106-0\_\_\_



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	15 – 60 kg
Readability [d]	5 – 20 g
Verification unit [e]	5 – 20 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55 / 65
Keypad	touch screen
Construction	Stainless steel
Communication interface	
Communication interface	RS232, USB, Ethernet, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions	
Operating temperature	-10 – +40 °C
Components and software	
Operating system	Microsoft Windows 11 IoT
Features of use	
Capacity	max 100 pcs/min
Conveyor velocity	0.1 – 1.7 m/s

\*OIML class for checkweighers used in packaged goods control (PGC) systems.



## Accessories (Additional Fee)

### Displays

Transponder card readers  
 RS 232 cables (scale - ZEBRA printer)  
 RS 232, RS 485 cables  
 Barcode scanners

### Label Printers

Keypad, external switches  
 USB adapter  
 Receipt Printer  
 USB cable (scale - printer)

## Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]