



More information on the website  
[mirror.radwag.com/en/info,w1,TG8](http://mirror.radwag.com/en/info,w1,TG8)

# PL/4N/1500/H3.LD Platform

WX-009-0247



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                         |
|--------------------------|-------------------------|
| Maximum capacity [Max]   | 1500 kg                 |
| Readability [d]          | 500 g                   |
| Construction             |                         |
| Protection class         | IP 66 / 69              |
| Construction             | Stainless steel AISI304 |
| Weighing pan material    | Stainless steel AISI304 |
| Physical parameters      |                         |
| Weighing pan dimensions  | 1200×1500 mm            |
| Weighing platform height | 77 mm                   |

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.



## Accessories (Additional Fee)

PUE 5 Weighing Terminal  
PUE HX7 Weighing Terminal

PUE 7.1 Weighing Terminal  
PUE HY10 Weighing Terminal

## Device dimensions W x D x H



| Model         | Max     | A    | B    | C    | C1 | D    | E    | F    | G    | H    |
|---------------|---------|------|------|------|----|------|------|------|------|------|
| PL/4N/150/H1  | 150 kg  | 840  | 860  | 45,5 | 76 | 1040 | 1710 | 778  | 940  | 1170 |
| PL/4N/300/H1  | 300 kg  | 840  | 860  | 45,5 | 76 | 1040 | 1710 | 778  | 940  | 1170 |
| PL/4N/600H1   | 600 kg  | 840  | 860  | 45,5 | 76 | 1040 | 1710 | 778  | 940  | 1170 |
| PL/4N/150H2   | 1500 kg | 1100 | 1200 | 45,5 | 76 | 1300 | 2050 | 1118 | 1200 | 1430 |
| PL/4N/300/H2  | 300 kg  | 1100 | 1200 | 45,5 | 76 | 1300 | 2050 | 1118 | 1200 | 1430 |
| PL/4N/600/H2  | 600 kg  | 1100 | 1200 | 45,5 | 76 | 1300 | 2050 | 1118 | 1200 | 1430 |
| PL/4N/1500/H2 | 1500 kg | 1100 | 1200 | 52,5 | 76 | 1300 | 2150 | 1118 | 1200 | 1430 |
| PL/4N/300/H3  | 300 kg  | 1200 | 1500 | 45,5 | 76 | 1400 | 2350 | 1418 | 1300 | 1530 |
| PL/4N/600/H3  | 600 kg  | 1200 | 1500 | 45,5 | 76 | 1400 | 2350 | 1418 | 1300 | 1530 |
| PL/4N/1500/H3 | 1500 kg | 1200 | 1500 | 52,5 | 76 | 1400 | 2450 | 1418 | 1300 | 1530 |
| PL/4N/300/H4  | 300 kg  | 1500 | 1500 | 52,5 | 76 | 1700 | 2450 | 1418 | 1600 | 1830 |
| PL/4N/600/H4  | 600 kg  | 1500 | 1500 | 52,5 | 76 | 1700 | 2450 | 1418 | 1600 | 1830 |
| PL/4N/1500/H4 | 1500 kg | 1500 | 1500 | 52,5 | 76 | 1700 | 2450 | 1418 | 1600 | 1830 |