



More information on the website  
[mirror.radwag.com/en/info,w1,TYD](http://mirror.radwag.com/en/info,w1,TYD)

# MA 110.X7.A.WH Moisture Analyzer

WL-308-0005



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	110 g
Readability [d]	1 mg
Tare range	-110 g
Linearity	±0.003 g
Stabilization time	max 3 s
Adjustment	external
Maximum sample weight	110 g

<b>Metrological parameters</b>	
Heating module	halogen
Moisture content repeatability	±0.05 % (sample ~ 2 g), ±0.01 % (sample ~ 10 g)
Moisture content readability	0.001 %
Drying temperature range	Max 250 °C
<b>Physical parameters</b>	
Leveling system	manual
Display	7" graphic colour touchscreen
Weighing chamber	automatic
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions W x D x H	476×381×346 mm
Net weight	5.2 kg
Gross weight	6.5 kg
<b>Construction</b>	
Protection class	IP 43
<b>Components and software</b>	
Database capacity	Products, Users, Packaging, Customers, Drying programs, Drying process reports, Ambient Conditions, Weighings
<b>Features of use</b>	
Display mode	%D, %M, %R, g
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
<b>Communication interface</b>	
Communication interface	2×RS232 <sup>1</sup> , USB-A, USB-B, Ethernet, Wi-Fi
<b>Electrical parameters</b>	
Power supply	100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz
Power consumption	6 W
Heating module power	450 W
<b>Environmental conditions</b>	
Operating temperature	+10 – +40 °C
Mass indication control	External mass standard 50g, 100g, 200g, depending on the type of moisture analyzer (additional equipment)
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)
<b>SOP – metrological tests (additional options)</b>	
Drying temperature control	One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set (additional equipment)

<sup>1</sup> Barcode scanners, available as weighing instrument accessory, communicate with the instrument via RS232 interface exclusively.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Antivibration Tables  
Moisture analyzer accessories  
Barcode scanners  
Protective cover for balances  
Receipt Printer

RS 232, RS 485 cables  
Additional modules  
RS 232 cables (scale - printer)  
RS 232 – RS 485 Converter

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

- E2R Moisture Analyzers [WX-010-0072]
- Scale Editor 2.1 [WX-010-0173]

## Device dimensions W x D x H

