



More information on the website  
[mirror.radwag.com/tr/info,w1,U3D](http://mirror.radwag.com/tr/info,w1,U3D)

## C315.4.3000.C8/9 Yer kantarı

WP-230-0015



The drawings, photos and graphics used are for illustrative purposes only.

### Fonksiyonlar



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit  
measurement



GLP Procedures



Animal weighing



ALIBI Memory

### Teknik Veriler

| Metrolojik parametreler                                     |          |
|-------------------------------------------------------------|----------|
| Maksimum yük [Max]                                          | 3000 kg  |
| Minimum yük [Min]                                           | 20 kg    |
| Okuma için doğruluğu [d]                                    | 1 kg     |
| Yasallaştırma birimi [e]                                    | 1 kg     |
| Dara aralığı                                                | -3000 kg |
| Ticari amaçla kullanılmayan terazi için maksimum hassasiyet | 200 g    |
| OIML sınıfı                                                 | III      |

| Fiziksel parametreler          |                                                          |
|--------------------------------|----------------------------------------------------------|
| Display                        | 4,3" LCD (aydınlatma ile)                                |
| Kablo uzunluğu                 | 3 m                                                      |
| Tartım kefesi boyutları        | 1200×1500 mm                                             |
| Tartım platformunun yüksekliği | 120 ± 10 mm                                              |
| Ambalaj boyutları G x D x Y    | 1600×1300×500 mm                                         |
| Göstergeli terazi kütlesi      | 135 kg                                                   |
| Konstrüksiyon                  |                                                          |
| IP Sınıfı                      | IP 65 konstrüksiyon, IP 67 gerinim ölçer, IP 43 terminal |
| Haberleşme arayüzler           |                                                          |
| Haberleşme arayüzü             | RS232                                                    |
| Opsiyonel arayüzler            | RS232                                                    |
| Elektrik parametreleri         |                                                          |
| Güç kaynağı                    | 100 – 240 V AC 50/60 Hz + batarya                        |
| Maksimum güç tüketimi          | 5 W                                                      |
| Batarya ile çalışma süresi     | max 8h                                                   |
| Çevresel koşullar              |                                                          |
| Çalıştırma sıcaklığı           | -10 – +40 °C                                             |
| Atmosferik nem                 | 10% – 85% RH yoğunlaşma yok                              |



Additional fee for verification



## Aksesuarlar (Additional Fee)

Güç adaptörü  
RS 232 Kablolar (Teraziler - Yazıcı)  
Tartım terminalleri için tutucular  
Çakmak prizine uygun besleme kabloları  
Teraziye yere batırmak için çerçeve  
Display  
Rampa


RS 232, RS 485 Kabloları  
RS 232 – Ethernet Dönüştürücü  
AP2-1 Güç döngüsü çıkışı  
RS 232 – USB Dönüştürücü  
Kablolar RS 232 (Teraziler - Yazıcı)  
RS 232 – RS 485 Dönüştürücü  
Fiş yazıcı

## Yazılım (Additional Fee)

• RAD Key [WX-010-0005]  
• Terazi Editörü - EWAG 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

Cihaz boyutları G x D x Y



|         | A    | B    | H       |
|---------|------|------|---------|
| C6      | 800  | 800  | 120 ±10 |
| C7      | 1000 | 1000 | 120 ±10 |
| C8      | 1200 | 1200 | 120 ±10 |
| C8/9    | 1200 | 1500 | 120 ±10 |
| C9      | 1500 | 1500 | 120 ±10 |
| 6000.C9 | 1500 | 1500 | 160 ±10 |