



More information on the website  
[mirror.radwag.com/it/info,w1,U4E](https://mirror.radwag.com/it/info,w1,U4E)

## Suction pump for liquids



The drawings, photos and graphics used are for illustrative purposes only.

### Caratteristiche generali

The product is supplied with two internal pumps and two built-in buttons used to operate separate pumps. Backlit buttons inform you about operation of a specific pump.

The set has two tips for sucking water out of a single beaker (one-channel tip) or four pipettes at a time (four-channel tip). Water is carried from both channels to the beaker through one tube.

The power is provided to the pump through a USB in the weighing terminal. You can supply power from the phone charger, for instance.

### Compatibile con

Bilance automatiche per la taratura delle pipette  
 Microbalance XA 5Y.M.A  
 Bilance analitiche XA 5Y.A

Bilance analitiche XA 5Y  
 Microbalance XA 5Y.M  
 Microbalance MYA 5Y