



More information on the website
mirror.radwag.com/us/info,w1,U4E

Suction pump for liquids

WX-001-0445



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Precision suction, error-free measurements The product is supplied with two internal pumps and two built-in buttons used to operate separate pumps. Backlit buttons inform you about operation of a specific pump. The set has two tips for sucking water out of a single beaker (one-channel tip) or four pipettes at a time (four-channel tip). Water is carried from both channels to the beaker through one tube. The power is provided to the pump through a USB A in the weighing terminal. You can supply power from the phone charger, for instance.

Compatible with (Additional Fee)

Automatic Balances for. Pipettes Calibration

XA 5Y.M.A Microbalance

XA 5Y.A Analytical Balance

XA 5Y Analytical Balance

XA 5Y.M Microbalance

MYA 5Y Microbalance