

## **Suction pump for liquids**

WX-001-0445





The drawings, photos and graphics used are for illustrative purposes only.

## **Overview**

Precision suction, error-free measurements The product is supplied with two internal pumps and two built-in buttons used to operate separate pumps. Backlit buttons inform you about operation of a specific pump. The set has two tips for sucking water out of a single beaker (one-channel tip) or four pipettes at a time (four-channel tip). Water is carried from both channels to the beaker through one tube. The power is provided to the pump through a USB A in the weighing terminal. You can supply power from the phone charger, for instance.

## **Compatible with (Additional Fee)**

Automatic Balances for. Pipettes Calibration XA 5Y.M.A Microbalance

XA 5Y Analytical Balance XA 5Y.M Microbalance