



# CY10.60.C2.K.M2 Precision Balance

WL-225-0013

More information on the website  
[mirror.radwag.com/us/info,w1,U71](http://mirror.radwag.com/us/info,w1,U71)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	60 kg
Minimum load	50 g
Readability [d]	1 g
Verification unit [e]	10 g
Tare range	-60 kg
Repeatability	1,5 g
Linearity	±3 g

Metrological parameters	
Stabilization time	3 s
Adjustment	external
OIML Class	II
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	2,5 m
Weighing pan dimensions	400×500 mm
Packaging dimensions W x D x H	720×620×210 mm
Net weight	13,5 kg
Gross weight	16 kg
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10–19W*
Environmental conditions	
Operating temperature	+15 – +30 °C
Storage temperature	-25 – +70 °C
Relative humidity	10% – 80% RH no condensation

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

### MediaBox

Mild steel powder coated weighing platforms  
HRP Platforms High Capacity  
RFID Tags  
Antivibration tables  
Power Adapters  
Additional Weighing platforms Module  
Additional modules  
Platforms in plastic casing

### Professional Weighing Tables

Protective cover for balances  
Barcode scanners  
RS 232, RS 485 cables  
Label Printers  
Stands, wall mounting kits and mounting brackets  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions W x D x H

