

PL/4/1500/H7 プラットフォーム

WX-009-0039





The drawings, photos and graphics used are for illustrative purposes only.


データシート

計測パラメータ	
最大ひょう量 [Max]	1500 kg
最小表示 [d]	500 g
工事中	
保護クラス	IP 66 / 69
工事中	いいえ AISI304
計量皿の材質	いいえ AISI304
物理的パラメータ	
計量皿寸法	1000×1000 mm
計量プラットフォームの高さ	88 mm



アクセサリ (Additional Fee)


デバイスの寸法 幅x奥行x高さ




Platform	Α	В	Н
PLC/4/C6	800	800	120 ±10
PLC/4/C7	1000	1000	120 ±10
PLC/4/C8	1200	1200	120 ±10
PLC/4/C8/9	1200	1500	120 ±10
PLC/4/C9	1500	1500	120 ±10
PLC/4/C10	1500	2000	120 ±10
PLC/4/C11	2000	2000	120 ±10

dimensions in mm


PLC/4/C



PL/4/H6/Z PL/4/H7/Z PL/4/H8/Z



PL/4/H8/9/Z PL/4/H9/Z PL/4/H10/Z




Platform	А	В	Н
PL/4/H6	800	800	88 ±2
PL/4/H7	1000	1000	88 ±2
PL/4/H8	1200	1200	88 ±2
PL/4/H8/9	1200	1500	88 ±2
PL/4/H9	1500	1500	88 ±2
PL/4/H10	1500	2000	111 ±2

Α

dimensions in mm

PL/4/H



Platform	A	В	Н
PL/4/H6/Z	800	800	88 ±2
PL/4/H7/Z	1000	1000	88 ±2
PL/4/H8/Z	1200	1200	88 ±2
PL/4/H8/9/Z	1200	1500	88 ±2
PL/4/H9/Z	1500	1500	88 ±2
PL/4/H10/Z	1500	2000	111 ±2

dimensions in mm

PL/4/H/Z