



More information on the website  
[mirror.radwag.com/en/info,w1,UMJ](http://mirror.radwag.com/en/info,w1,UMJ)

## CK-02/1 Transponder Card Reader

WX-004-0151



The drawings, photos and graphics used are for illustrative purposes only.

### Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/1 is designed for scales equipped with terminal TMC series (scales in CPG systems, etc). It is installed close to the scale. Communication through RS 232 interface, power supply +5V DC from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminal TMC series (scales in CPG systems, etc). It is installed close to the scale. Communication through RS 232 interface, power supply +5V DC from scale terminal.

### Compatible with (Additional Fee)

HY10.H Scales for PGC