



More information on the website  
[mirror.radwag.com/us/info,w1,UMJ](https://mirror.radwag.com/us/info,w1,UMJ)

# CK-02/1 Transponder Card Reader

WX-004-0151



The drawings, photos and graphics used are for illustrative purposes only.

## Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/1 is designed for scales equipped with terminal TMC series (scales in CPG systems, etc). It is installed close to the scale. Communication through RS 232 interface, power supply +5V DC from scale terminal.

**Area of Use:** • Additional equipment of load cell based industrial scales; • Identification of weighing instrument operator; • Identification of vehicles on weighbridges.

**Design:** Transponder card reader CK-02 is manufactured in plastic housing.

### Intended Use:

Designed for scales equipped with terminal TMC series (scales in CPG systems, etc). It is installed close to the scale. Communication through RS 232 interface, power supply +5V DC from scale terminal.

## Compatible with (Additional Fee)

HY10.H scales for PGC