



More information on the website  
[mirror.radwag.com/tr/info,w1,UVW](http://mirror.radwag.com/tr/info,w1,UVW)

## CK-02/2 Transponder Card Reader

WX-005-0012



The drawings, photos and graphics used are for illustrative purposes only.

### Genel Açıklama

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/2 is designed for weighbridges equipped with terminal TMC series. It is installed in a large distance from the terminal (e.g. next to the barriers). Communication through RS485, power supply 9-24V AC from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing with stainless steel mounting kit. There are two mounting kits offered, depending on model. Intended Use: Designed for weighbridges equipped with terminal TMC series. It is installed in a large distance from the terminal (e.g. next to the barriers). Communication through RS485, power supply 9-24V AC from scale terminal.