



# CK-02/2 Transponder Card Reader

WX-005-0012

More information on the website  
[mirror.radwag.com/us/info,w1,UVW](https://mirror.radwag.com/us/info,w1,UVW)



The drawings, photos and graphics used are for illustrative purposes only.

## Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/2 is designed for weighbridges equipped with terminal TMC series. It is installed in a large distance from the terminal (e.g. next to the barriers). Communication through RS485, power supply 9-24V AC from scale terminal. **Area of Use:** • Additional equipment of load cell based industrial scales; • Identification of weighing instrument operator; • Identification of vehicles on weighbridges.

**Design:** Transponder card reader CK-02 is manufactured in plastic housing with stainless steel mounting kit. There are two mounting kits offered, depending on model.

### Intended Use:

Designed for weighbridges equipped with terminal TMC series. It is installed in a large distance from the terminal (e.g. next to the barriers). Communication through RS485, power supply 9-24V AC from scale terminal.