



# MW-04-1 Mass Converter

WX-016-0035

More information on the website  
[mirror.radwag.com/us/info,w1,UWS](http://mirror.radwag.com/us/info,w1,UWS)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Construction	
Protection class	IP 65
Housing	aluminum
Communication interface	
Communication interface	RS232, Ethernet, 4IN/4OUT
Power supply	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	25 W
Maximum quantity of divisions from converter	838 860 ×10
Minimum volatge per verification unit	0,4 μV
Minimum load cell impedance	80 Ω
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V DC
Maximum increase of signal	19,5 mV
Connection of load cells	4 or 6 wires + ekran

Operating temperature	-10 – +40 °C
<b>Physical parameters</b>	
Packaging dimensions W x D x H	300×250×130 mm
Net weight	2,5 kg
Gross weight	3,32 kg
Multiple range	YES
<b>Features of use</b>	
Max number of platforms	2 (max 4)

## Compatible with (Additional Fee)

Additional Weighing platforms Module


RS 232 – USB Converter

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- RADWAG Development Studio [WX-010-0104]

- MW Manager [WX-010-0113]

## Device dimensions W x D x H



MW-04