



More information on the website  
[mirror.radwag.com/us/info,w1,UY9](https://mirror.radwag.com/us/info,w1,UY9)

# HX5.EX-1.30.F1 One Load Cell Platform Scale

WW-006-0005



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

| Physical parameters    |                   |
|------------------------|-------------------|
| Maximum capacity [Max] | 30 kg             |
| Minimum load           | 200 g             |
| Readability [d]        | 10 g              |
| Tare range             | -30 kg            |
| OIML Class             | III               |
| Physical parameters    |                   |
| Display                | 5" graphic colour |

| Physical parameters            |                                         |
|--------------------------------|-----------------------------------------|
| Cable length                   | 1 m                                     |
| Weighing pan dimensions        | 300×300 mm                              |
| Packaging dimensions W x D x H | 390×640×390 mm                          |
| Net weight                     | 13,22 kg                                |
| Gross weight                   | 15,5 kg                                 |
| Construction                   |                                         |
| Protection class               | IP 65 construction, IP 66 / 68 terminal |
| ATEX Certification             | II 2G Ex ib IIB T4 Gb                   |
| IECEX Certification            | Ex ic IIB T4 Gc                         |
| Construction                   | mild steel St3S                         |
| Weighing pan material          | Stainless steel AISI304                 |
|                                |                                         |
| Communication interface        | 2×RS232, RS485                          |
|                                |                                         |
| Power supply                   | 100 – 240 V AC 50/60 Hz                 |
| Power consumption max.         | 15 W                                    |
|                                |                                         |
| Operating temperature          | -10 – +40 °C                            |
| Relative humidity              | 10% – 85% RH no condensation            |
| Indicator                      | PUE HX5.EX-1                            |



Additional fee for verification



## Accessories (Additional Fee)

Communication modules  
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
Weighing Terminal

Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]