



More information on the website
mirror.radwag.com/en/info,w1,VBJ

CY10.6/12.F1.K Precision Balance

WL-225-1002



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

Datasheet

| Metrological parameters | |
|-------------------------|-------------|
| Maximum capacity [Max] | 6 / 12 kg |
| Minimum load | - |
| Readability [d] | 0.1 / 0.2 g |
| Verification unit [e] | - |
| Tare range | -12 kg |
| Repeatability | 0.6 g |
| Linearity | ±0.1 g |

| Metrological parameters | |
|---------------------------------|--|
| Stabilization time | 3 s |
| Adjustment | external |
| OIML Class | - |
| Physical parameters | |
| Leveling system | manual |
| Display | 10" graphic colour touchscreen |
| Cable length | 1 m |
| Weighing pan dimensions | 300×300 mm |
| Packaging dimensions W x D x H | 570×390×170 mm |
| Net weight | 6.2 kg |
| Gross weight | 7 kg |
| Construction | |
| Protection class | IP 43 |
| Housing | steel + ABS |
| Communication interface | |
| Communication interface | 2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot |
| Electrical parameters | |
| Power supply | Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max; 10–19W* |
| Environmental conditions | |
| Operating temperature | +15 – +30 °C |
| Storage temperature | -25 – +70 °C |
| Relative humidity | 10% – 80% RH no condensation |

*Power consumption depends on the terminal configuration and the number and type of external devices connected.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Antivibration Tables
Power Adapters
Additional Weighing platforms Module
Additional modules
Platforms in plastic casing
Professional Weighing Tables

Protective cover for balances
Barcode scanners
RS 232, RS 485 cables
Label Printers
Stands, wall mounting kits and mounting brackets
Fingerprint Reader
RS 232 – USB Converter
Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions W x D x H

