



More information on the website
mirror.radwag.com/ja/info,w1,VIE

WPY 60/C2/K 多機能はかり

WP-111-0004



The drawings, photos and graphics used are for illustrative purposes only.

機能

-  Dosing
-  Labelling
-  Plus/Minus Control
-  Percent Weighing
-  Totalizing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Animal weighing
-  Differential weighing
-  ALIBI Memory

データシート

| 計測パラメータ | |
|--------------------|--------|
| 最大ひょう量 [Max] | 60 kg |
| 最小荷重 | 400 g |
| 最小表示 [d] | 20 g |
| 法定計量時の単位 [e] | 20 g |
| 風袋範囲 | -60 kg |
| 非検定用はかりの最大可読性 (目量) | 2 g |

| 計測パラメータ | |
|--------------|--|
| 安定化時間 | 2 s |
| 調整 | ワイヤー + シールド |
| OIMLクラス | III |
| 物理的パラメータ | |
| ディスプレイ | 5インチグラフィックカラータッチスクリーン |
| 計量皿寸法 | 400×500 mm |
| 梱包寸法 幅×奥行×高さ | 720×620×210 mm |
| 正味重量 | 11,1 kg |
| 総重量 | 13,1 kg |
| 工事中 | |
| 保護クラス | IP 65 ステンレススチール, IP 43 円筒形 |
| 通信インターフェース | |
| 通信インターフェース | 2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (IN), Wi-Fi |
| 電気的パラメータ | |
| 電源 | 100 – 240 V AC 50/60 Hz |
| 環境条件 | |
| 動作温度 | -10 – +40 °C |

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



アクセサリ (Additional Fee)

トランスポンダー式カードリーダー
RS 232 ケーブル (はかり - プリンタ)
シガーライターソケット電源ケーブル
バーコードスキャナ
RS 232、RS 485 ケーブル
ラベルプリンタ
防振台
ディスプレイ

IN/OUT ケーブル
キーボード、外部スイッチ
スタンド、壁取り付けキット、取り付けブラケット
レシートプリンタ
F1 級分銅 - 調整室なしノブ型分銅、セット
AP2-1 電流ループユニット
追加計量プラットフォームモジュール
RS 232 - USB コンバータ

ソフトウェア (Additional Fee)

- E2R Weighing (計量) [WX-010-0099]
- Audit Trail Reader (監査証跡) [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

デバイスの寸法 幅x奥行x高さ



WPY C2/K
