



More information on the website  
[mirror.radwag.com/en/info,w1,VUW](http://mirror.radwag.com/en/info,w1,VUW)

# DWT/RC HY Checkweigher

WK-106-0\_\_\_



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	10 – 600 kg
Minimum load	0.1 – 4 kg
Readability [d]	5 – 200 g
Tare range	-10 – -600 kg
Physical parameters	
Display	10.1" graphic colour touchscreen
Construction	
Protection class	IP 66 / 67
Communication interface	
Communication interface	RS232, RS485
Environmental conditions	
Operating temperature	-10 – +40 °C

## Features of use

Capacity	max 50 pcs/min
Conveyor velocity	0.1 – 0.5 m/s
Speed	0.1 – 0.5 m/s



## Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]