



More information on the website  
[mirror.radwag.com/us/info,w1,VUW](http://mirror.radwag.com/us/info,w1,VUW)

# DWT/RC HY Checkweigher

WK-106-000\_



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	15 – 60 kg
Readability [d]	5 – 20 g
Verification unit [e]	5 – 20 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	10,1" graphic colour touchscreen
Construction	
Protection class	IP 55 / 65
Keypad	touch screen
Construction	Stainless steel
Communication interface	
Communication interface	RS232, RS485, Ethernet, USB, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions	
Operating temperature	-10 – +40 °C
Components and software	
Operating system	Linux
Features of use	
Capacity	max 100 pcs/min
Conveyor velocity	0,1 – 1,7 m/s



## Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

!Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]