



More information on the website
mirror.radwag.com/en/info,w1,W9Z

P0151 Cable



The drawings, photos and graphics used are for illustrative purposes only.

Overview

RS 232 cable for connecting a balance/scale (PUE C/31 terminal) to an Epson printer. Standard cable length: 1,7m. Compatible with:

- Scales operated by means of PUE C31 terminal
- Scales operated by means of PUE 7.1 terminal
- PUE C31 terminal
- PUE 7.1 terminal

Compatible with

H315 HR Waterproof Platform Scale
 MA X7.IC.A Moisture Analyzer
 MUYA Modules
 WPY Multifunctional Scale
 C32 Multifunctional Scale
 MA 5Y Moisture Analyzer
 C315 Platform scale
 WLY Scales for PGC
 MA X2.IC.A Moisture Analyzers
 AS X7 Analytical Balance

MA R Moisture Analyzer
 AS 5Y Analytical Balance
 AK-4 Automatic Mass Comparator
 PS 5Y Balances for PGC
 AKM-2 Automatic Mass Comparator
 PS R2.H Precision Balance
 WTC Precision Balance
 H315 4C Platform Scale
 WLY Precision Balance
 UMA Automatic Mass Comparator

PS X2 Precision Balance
AS X2 PLUS Analytical Balances
PS X7 Balances for PGC
WLC Precision Balance
PS R2 Precision Balance
C315.4P2 Beam Scales
WLC X7 Precision Balance
PS X2 Balances for PGC
MA X2.A Moisture Analyzers
MAS Modules
MPS Modules
C315.4 Platform Scale
C32.PM Precision Balance
MA X7.A Moisture Analyzer
PS X7 Precision Balance
WPY Scales for PGC
C315.4P pallet scales
WAY 5Y.KO Manual Mass Comparator
MA 5Y.IC Moisture Analyzer

APP 5Y.KO Manual Mass Comparator
Robotic Mass Comparators
Density Measurement
WLC C/2 Precision Balance
PS R1 Precision Balance
5Y.PM.KB Manual Mass Comparator
AS R2 PLUS Analytical Balance
PUE 7.1 Weighing Terminal
PS 5Y Precision Balance
Postal Scales for Packages
Automatic Vacuum Mass Comparators
MAS1 Modules
PMV 5Y Moisture Analyzer
XA 5Y.KO Manual Mass Comparator
PUE C315 Weighing Terminal
UYA 5Y.KO Manual Mass Comparator
AS R1 PLUS Analytical Balance
Nano-Comparator NANO.AK-4.500.5Y