



More information on the website
mirror.radwag.com/ja/info,w1,W9Z

P0151

WX-013-0002



The drawings, photos and graphics used are for illustrative purposes only.

☒☒

RS232 PUE C31 / Epson 1,7m :

- PUE C31
- PUE 7.1
- PUE C31
- PUE 7.1

☒☒☒☒ (Additional Fee)

- H315 HR
- MA X7.IC.A
- MUYA
- WPY
- C32
- MA 5Y
- C315
- PGC WLY
- MA X2.IC.A
- AS X7
- PS X2

- MA R
- AS 5Y
- AK-4
- PGC PS 3Y
- AKM-2
- PS R2.H
- WTC
- H315 4C
- WLY
- UMA
- APP 5Y.KO

AS X2 PLUS
PGC PS X7
WLC
PS R2
C315.4P2
WLC X7
PGC PS X2
MA X2.A
MAS
MPS
C315.4
C32.PM
MA X7.A
PS X7
PGC WPY
C315.4P
WAY 5Y.KO
MA 5Y.IC

WLC C/2
PS R1
5Y.PM.KB
AS R2 PLUS
PUE 7.1
PS 5Y
MAS1
PMV 5Y
XA 5Y.KO
PUE C315
UYA 5Y.KO
AS R1 PLUS
Nano-Comparator NANO.AK-4.500.5Y