



More information on the website
mirror.radwag.com/de/info,w1,WPH

Bodeneinbauwaage HX5.EX- 1.4.3000.H9/Z

WW-008-0045



The drawings, photos and graphics used are for illustrative purposes only.

Funktionen



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit
measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Technische Daten

Messtechnische Parameter	
Wägebereich [Max]	3000 kg
Min. Belastung	20 kg
Ablesbarkeit [d]	1 kg
Eichwert [e]	1 kg
Tarierbereich	-3000 kg
OIML-Klasse	III

Physikalische Parameter		
Display		5" grafisch farbiger
Kabellänge		3 m
Waagschale		1500×1500 mm
Nettogewicht		202,8 kg
Bruttogewicht		304 kg
Konstruktion		
Schutzart		IP 66 / 69 Konstruktion, IP 66 / 68 Terminal
Zertifizierung ATEX		II 2G Ex ib IIB T4 Gb
Zertifizierung IECEx		Ex ib IIB T4 Gb
Konstruktion		Edelstahl AISI304
Kommunikationsschnittstellen		
Schnittstellen		2×RS232, RS485
Elektrische Parameter		
Stromversorgung		100 – 240 V AC 50/60 Hz
Maximaler Leistungsaufnahme		15 W
Umgebungsbedingungen		
Umgebungstemperatur		-10 – +40 °C
Relative Luftfeuchtigkeit		10% – 85% RH ohne Kondensation
Messgerät		PUE HX5.EX-1



Additional fee for verification



Zubehör (Additional Fee)

Kommunikationsmodul
Eigensichere Stromversorgung für EX-Waage

Thermische Drucker

Software (Additional Fee)

- E2R Wägung [WX-010-0099]
- Etiketten-Editor R02 [WX-010-0094]
- RLAB [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]