



More information on the website
mirror.radwag.com/us/info,w1,WPH

HX5.EX-1.4.3000.H9/Z 4 Load Cell Platform Scale, pit version

WW-008-0045



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit
measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	3000 kg
Minimum load	20 kg
Readability [d]	1 kg
Verification unit [e]	1 kg
Tare range	-3000 kg
OIML Class	III

Physical parameters		
Display		5" graphic colour
Cable length		3 m
Weighing pan dimensions		1500×1500 mm
Net weight		202,8 kg
Gross weight		304 kg
Construction		
Protection class		IP 66 / 69 construction, IP 66 / 68 terminal
ATEX Certification		II 2G Ex ib IIB T4 Gb
IECEx Certification		Ex ib IIB T4 Gb
Construction		Stainless steel AISI304
Communication interface		
Communication interface		2×RS232, RS485
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz
Power consumption max.		15 W
Environmental conditions		
Operating temperature		-10 – +40 °C
Relative humidity		10% – 85% RH no condensation
Indicator		PUE HX5.EX-1



Additional fee for verification



Accessories (Additional Fee)

Communication modules

Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX

Weighing Terminal

Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]